

“DRIPLESS” SAFE-T-FEED™

The Ultimate in Safety tote dispensing! No product exposure, odor, or safety issues. Both the tote male fitting and the feed line female fitting have integral spring-loaded check valves for positive engage and disengage operations.

Simply press the thumb-release spring on the female adaptor and push onto the tote’s male fitting and you are done! The venting device on the opposite side of the tote will allow vent/relief to accommodate any discharge rate without collapsing the tote.

The standard dispensing device includes a 1/4” stainless tube that goes all the way to the lowest portion of the tote. High removal rates (higher than 2-3 gal/min) may require larger suction fittings that are available on request.

We are committed to your safety. However, these devices are only available on our heavy-duty returnable-quality totes.

